



## Eaton 163933

Eaton Distribution parts. Fuse switch  
disconnecter, 3p, NH00, AC23, 11C075BMC

□□□□

|                             |                          |
|-----------------------------|--------------------------|
| <b>PRODUCT NAME</b>         | Eaton Distribution parts |
| <b>CATALOG NUMBER</b>       | 163933                   |
| <b>PRODUCT LENGTH/DEPTH</b> | 590 mm                   |
| <b>PRODUCT HEIGHT</b>       | 49.5 mm                  |
| <b>PRODUCT WIDTH</b>        | 280 mm                   |
| <b>PRODUCT WEIGHT</b>       | 4.845 kg                 |
| <b>COMPLIANCES</b>          | RoHS conform             |

|                                                        |                                |
|--------------------------------------------------------|--------------------------------|
| <b>FEATURES</b>                                        | Motor drive optional           |
| <b>FITTED WITH:</b>                                    | Connectors<br>Error protection |
| <b>RATED OPERATIONAL POWER AT AC-23A, 400 V, 50 HZ</b> | 0 kW                           |
| <b>RATED PERMANENT CURRENT (IU)</b>                    | 160 A                          |
| <b>RATED UNINTERRUPTED CURRENT (IU)</b>                | 160 A                          |
| <b>CONDITIONED RATED SHORT-CIRCUIT CURRENT IQ</b>      | 100 kA                         |
| <b>WITH ERROR PROTECTION</b>                           | Yes                            |
| <b>NUMBER OF POLES</b>                                 | Three-pole                     |
| <b>RATED OPERATION POWER AT AC-23, 400 V</b>           | 0 kW                           |
| <b>RATED SHORT-TIME WITHSTAND CURRENT (ICW)</b>        | 0 kA                           |
| <b>ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT</b>      | Screw connection               |
| <b>ACTUATOR POSITION</b>                               | Front side                     |
| <b>ACTUATOR TYPE</b>                                   | Long turning handle            |
| <b>SUITABLE FOR</b>                                    | Front mounting                 |
| <b>RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)</b>    | 100 kA                         |
| <b>SUITABLE FOR FUSES</b>                              | NH00                           |
| <b>CABLE ENTRY TYPE</b>                                | Side                           |
| <b>DEGREE OF PROTECTION (FRONT SIDE)</b>               | IP40                           |
| <b>POWER RATING AT AC-23, 400 V</b>                    | 0 kW                           |
| <b>RATED OPERATING VOLTAGE (UE) AT AC - MAX</b>        | 690 V                          |

|                 |
|-----------------|
| PROJECT NAME:   |
| PROJECT NUMBER: |
| PREPARED BY:    |
|                 |



  Eaton House  
30 Pembroke Road  
Dublin 4,    
Eaton.com

© 2025    

Follow us on social media to get the latest product and support information.

