



Eaton 163940

Eaton Distribution parts. Fuse switch
disconnecter, 3p, NH00, AC23,
11C105BMCAE

□□□□

PRODUCT NAME	Eaton Distribution parts
CATALOG NUMBER	163940
PRODUCT LENGTH/DEPTH	590 mm
PRODUCT HEIGHT	49.5 mm
PRODUCT WIDTH	280 mm
PRODUCT WEIGHT	4.99 kg
COMPLIANCES	RoHS conform

FEATURES	Motor drive optional
FITTED WITH:	Connectors Error protection
RATED OPERATIONAL POWER AT AC-23A, 400 V, 50 HZ	0 kW
RATED PERMANENT CURRENT (IU)	160 A
RATED UNINTERRUPTED CURRENT (IU)	160 A
CONDITIONED RATED SHORT-CIRCUIT CURRENT IQ	100 kA
WITH ERROR PROTECTION	Yes
NUMBER OF POLES	Three-pole
RATED OPERATION POWER AT AC-23, 400 V	0 kW
RATED SHORT-TIME WITHSTAND CURRENT (ICW)	0 kA
ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Screw connection
ACTUATOR POSITION	Front side
ACTUATOR TYPE	Long turning handle
SUITABLE FOR	Front mounting
RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)	100 kA
SUITABLE FOR FUSES	NH00
CABLE ENTRY TYPE	Side
DEGREE OF PROTECTION (FRONT SIDE)	IP40
POWER RATING AT AC-23, 400 V	0 kW
RATED OPERATING VOLTAGE (UE) AT AC - MAX	690 V

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

