

Eaton 163980

Eaton Distribution parts. Fuse switch
disconnecter, 3p, NH00, AC23, 31C105BMCA

| | |
|-------------------------|--------------------------|
| | |
| PRODUCT NAME | Eaton Distribution parts |
| CATALOG NUMBER | 163980 |
| PRODUCT LENGTH/DEPTH | 590 mm |
| PRODUCT HEIGHT | 49.5 mm |
| PRODUCT WIDTH | 280 mm |
| PRODUCT WEIGHT | 5.253 kg |
| COMPLIANCES | RoHS conform |

| | |
|--|--------------------------------|
| | |
| FEATURES | Motor drive optional |
| FITTED WITH: | Connectors Error protection |
| RATED OPERATIONAL POWER AT AC-23A, 400 V, 50 HZ | 0 kW |
| RATED PERMANENT CURRENT (IU) | 160 A |
| RATED UNINTERRUPTED CURRENT (IU) | 160 A |
| CONDITIONED RATED SHORT-CIRCUIT CURRENT IQ | 100 kA |
| WITH ERROR PROTECTION | Yes |
| NUMBER OF POLES | Three-pole |
| RATED OPERATION POWER AT AC-23, 400 V | 0 kW |
| RATED SHORT-TIME WITHSTAND CURRENT (ICW) | 0 kA |
| ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT | Screw connection |
| ACTUATOR POSITION | Front side |
| ACTUATOR TYPE | Long turning handle |
| SUITABLE FOR | Front mounting |
| RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ) | 100 kA |
| SUITABLE FOR FUSES | NH00 |
| CABLE ENTRY TYPE | Side |
| DEGREE OF PROTECTION (FRONT SIDE) | IP40 |
| POWER RATING AT AC-23, 400 V | 0 kW |
| RATED OPERATING VOLTAGE (UE) AT AC - MAX | 690 V |

| | |
|-----------------------------------|--------------------------------|
| | |
| DECLARATIONS OF CONFORMITY | DA-DC-03 PIFT0 |

| |
|-----------------|
| PROJECT NAME: |
| PROJECT NUMBER: |
| PREPARED BY: |
| : |



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

