



Eaton 166987

Eaton Moeller® series CSDS Connection cable, 5p, DC current, coupling M12 flat, open end, L=10m

□□□□

PRODUCT NAME	Eaton Moeller® series CSDS Accessory Connection cable
CATALOG NUMBER	166987
PRODUCT LENGTH/DEPTH	190.5 mm
PRODUCT HEIGHT	40 mm
PRODUCT WIDTH	190.5 mm
PRODUCT WEIGHT	0.03 kg
COMPLIANCES	CE



Powering Business Worldwide

□□□□

TYPE	Connecting cables
NUMBER OF POLES	Five-pole
CABLE TYPE	Multi-core Coupling, straight, Input side Cable end, open, Output side
CONTACT SURFACE MATERIAL	Other
RATED OPERATIONAL VOLTAGE (UE) - MAX	0 V
PRODUCT CATEGORY	Accessories
VOLTAGE TYPE	DC
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
CONTINUITY RESISTOR	0 mΩ
NOMINAL CURRENT	0 A
CABLE LENGTH	10 m
CABLE SHEATH MATERIAL	Other
DEGREE OF PROTECTION	Other
COLOR CABLE SHEATH	Yellow
ELECTRICAL CONNECTION TYPE (BOX-SIDED)	Other
ELECTRICAL CONNECTION TYPE (FIELD-SIDED)	M12
CONTACT BODY MATERIAL	Other
PERMITTED TEMPERATURE OF OUTER CABLE (ASSEMBLED) WITHOUT VIBRATION - MAX	70 °C
PERMITTED TEMPERATURE OF OUTER CABLE (ASSEMBLED) WITHOUT VIBRATION - MIN	40 °C
PERMITTED TEMPERATURE OF OUTER CABLE (ASSEMBLING/HANDLING) - MAX	70 °C
PERMITTED	40 °C

□□

□□□	eaton-proximity-switches-csdr-connecting-cable-wiring-diagram-004.eps
□□	eaton-proximity-switches-csds-connecting-cable-3d-drawing.eps

TEMPERATURE OF OUTER CABLE (ASSEMBLING/HANDLING) - MIN	
PLUG-IN CONTACT TYPE (BOX-SIDED)	Male (plug)
PLUG-IN CONTACT TYPE (FIELD-SIDED)	Female (bus)
POSITIONING CABLE FEED (BOX-SIDED)	Other
POSITIONING CABLE FEED (FIELD-SIDED)	Straight

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
DATE: