



□□□□□

Eaton 168833

Eaton Distribution parts. Phase busbar, N, 16qmm, fork connector, 1m, 1,5MU

□□□□

PRODUCT NAME	Eaton Distribution parts
CATALOG NUMBER	168833
PRODUCT LENGTH/DEPTH	1012 mm
PRODUCT HEIGHT	35 mm
PRODUCT WIDTH	7 mm
PRODUCT WEIGHT	0.29 kg
COMPLIANCES	RoHS conform

□□□□

USED WITH	BB-EV Busbar
TYPE	• BB-EV • Busbar
FEATURES	Insulated Can be cut to size
ACCESSORY/SPARE PART TYPE	Busbar for combined residual current/power circuit breaker Busbar for TVSS Busbar for miniature circuit breaker Busbar for residual current circuit breakers
ELECTRIC CONNECTION TYPE	Fork
RATED SURGE VOLTAGE	4.5 kV
RATED UNINTERRUPTED CURRENT (IU)	80 A
SUITABLE FOR NUMBER OF DEVICES	12
APPLICATION	Switchgear for industrial and advanced commercial applications
NUMBER OF POLES	Two-pole
COLOR	Other
RATED SHORT-TIME WITHSTAND CURRENT (ICW)	0 kA
CROSS SECTION	16 mm ²
NUMBER OF MODULAR SPACINGS	1.5
NUMBER OF PHASES	1
PITCH DIMENSIONS	27 mm
RATED OPERATIONAL VOLTAGE (UE) - MAX	690 V
RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)	0 kA
FUNCTIONS	Busbar
SUITABLE FOR	Devices with N-busbar

□□

□□□	eaton-wiring-diagram-versch.jpg
□□	eaton-dimensions-mas-zv7-80a.jpg

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

