



□□□□□

## Eaton 168836

Eaton Distribution parts. Phase busbar, N, 10qmm, fork connector, 1m, 2MU

□□□□

PRODUCT NAME	Eaton Distribution parts
CATALOG NUMBER	168836
PRODUCT LENGTH/DEPTH	1000 mm
PRODUCT HEIGHT	35 mm
PRODUCT WIDTH	7 mm
PRODUCT WEIGHT	0.22 kg
COMPLIANCES	RoHS conform

## □□□□

### TYPE

- BB-EV
- Busbar

### FEATURES

Insulated  
Can be cut to size

### ACCESSORY/SPARE PART TYPE

Busbar for combined residual current/power circuit breaker  
Busbar for TVSS  
Busbar for miniature circuit breaker  
Busbar for residual current circuit breakers

### ELECTRIC CONNECTION TYPE

Fork

### RATED SURGE VOLTAGE

4.5 kV

### RATED UNINTERRUPTED CURRENT (IU)

63 A

### SUITABLE FOR NUMBER OF DEVICES

39

### APPLICATION

Switchgear for industrial and advanced commercial applications

### NUMBER OF POLES

Two-pole

### COLOR

Other

### RATED SHORT-TIME WITHSTAND CURRENT (ICW)

0 kA

### CROSS SECTION

10 mm<sup>2</sup>

### NUMBER OF MODULAR SPACINGS

2

### NUMBER OF PHASES

1

### PITCH DIMENSIONS

36 mm

### RATED OPERATIONAL VOLTAGE (UE) - MAX

690 V

### RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)

0 kA

### FUNCTIONS

Busbar

### SUITABLE FOR

Devices with N-busbar

## □□

### □□□

[eaton-wiring-diagram-versch.jpg](#)

### □□

[eaton-dimensions-mas-zv7-50a.jpg](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



  Eaton House  
30 Pembroke Road  
Dublin 4,    
Eaton.com

© 2025    

Follow us on social media to get the latest product and support information.

