



□□□□□

## Eaton 168848

Eaton Distribution parts. Phase busbar, 3-phase+HS, 10qmm, fork connector, 1m, 1MU/2AUX

□□□□

PRODUCT NAME	Eaton Distribution parts
CATALOG NUMBER	168848
PRODUCT LENGTH/DEPTH	1000 mm
PRODUCT HEIGHT	35 mm
PRODUCT WIDTH	15 mm
PRODUCT WEIGHT	0.53 kg
COMPLIANCES	RoHS conform

**TYPE**

- BB-EV
- Busbar

**FEATURES**

Insulated  
Can be cut to size

**ACCESSORY/SPARE PART TYPE**

Busbar for miniature circuit breaker  
Busbar for residual current circuit breakers  
Busbar for TVSS  
Busbar for combined residual current/power circuit breaker

**ELECTRIC CONNECTION TYPE**

Fork

**RATED SURGE VOLTAGE**

4.5 kV

**RATED UNINTERRUPTED CURRENT (IU)**

63 A

**SUITABLE FOR NUMBER OF DEVICES**

0

**APPLICATION**

Switchgear for industrial and advanced commercial applications

**NUMBER OF POLES**

Three-pole

**COLOR**

Other

**RATED SHORT-TIME WITHSTAND CURRENT (ICW)**

0 kA

**CROSS SECTION**

10 mm<sup>2</sup>

**NUMBER OF MODULAR SPACINGS**

1

**NUMBER OF PHASES**

3

**PITCH DIMENSIONS**

0 mm

**RATED OPERATIONAL VOLTAGE (UE) - MAX**

690 V

**RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)**

0 kA

**FUNCTIONS**

Busbar

**SUITABLE FOR**

Devices with auxiliary switch

□□□ [eaton-wiring-diagram-versch.jpg](#)

□□ [eaton-dimensions-mas-zv7-50a.jpg](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



  Eaton House  
30 Pembroke Road  
Dublin 4,    
Eaton.com

© 2025    

Follow us on social media to get the latest product and support information.

