



□□□□□

Eaton 168867

Eaton Distribution parts. Phase busbar, 2-phase, 16qmm, pin, 1m, 1,5MU

□□□□

PRODUCT NAME	Eaton Distribution parts
CATALOG NUMBER	168867
PRODUCT LENGTH/DEPTH	1016 mm
PRODUCT HEIGHT	35 mm
PRODUCT WIDTH	15 mm
PRODUCT WEIGHT	0.465 kg
COMPLIANCES	RoHS conform

□□□□

USED WITH	Busbar BB-EV
TYPE	• BB-EV • Busbar
FEATURES	Insulated Can be cut to size
ACCESSORY/SPARE PART TYPE	Busbar for combined residual current/power circuit breaker Busbar for residual current circuit breakers Busbar for TVSS Busbar for miniature circuit breaker
ELECTRIC CONNECTION TYPE	Pin
RATED SURGE VOLTAGE	4.5 kV
RATED UNINTERRUPTED CURRENT (IU)	80 A
SUITABLE FOR NUMBER OF DEVICES	9
APPLICATION	Switchgear for industrial and advanced commercial applications
NUMBER OF POLES	Two-pole
COLOR	Other
RATED SHORT-TIME WITHSTAND CURRENT (ICW)	0 kA
CROSS SECTION	16 mm ²
NUMBER OF MODULAR SPACINGS	1.5
NUMBER OF PHASES	2
PITCH DIMENSIONS	27 mm
RATED OPERATIONAL VOLTAGE (UE) - MAX	690 V
RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)	0 kA
FUNCTIONS	Busbar

□□

□□□	eaton-wiring-diagram-versch.jpg
□□	eaton-dimensions-mas-zv7-80a.jpg

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

