



## Eaton 17.5TDLSJ40

Eaton Bussmann series medium voltage DIN fuse, 40 A, 17.5 kV, 35.5 kA, 51 x 292 mm, With Striker

□□□□

<b>PRODUCT NAME</b>	Eaton Bussmann series medium voltage DIN fuse
<b>CATALOG NUMBER</b>	17.5TDLSJ40
<b>UPC</b>	051712525411
<b>PRODUCT LENGTH/DEPTH</b>	292 mm
<b>PRODUCT HEIGHT</b>	51 mm
<b>PRODUCT WIDTH</b>	51 mm
<b>PRODUCT WEIGHT</b>	1700 g
<b>COMPLIANCES</b>	DIN 43625 VDE 0670-4 IEC 60282-1
<b>CERTIFICATIONS</b>	KEMA Certified



Powering Business Worldwide

<b>USED WITH</b>	270303 Fuse clip A3354710 Fuse clip
<b>AMPERAGE RATING</b>	40 A
<b>FUSE INDICATOR</b>	With Striker
<b>FUSE SIZE</b>	51 x 292 mm
<b>BREAKING CAPACITY</b>	35.5 kA
<b>INSTALLATION TECHNIQUE</b>	Air
<b>PERFORMANCE CAT ACCORDING TO IEC 60282-1</b>	Back-up
<b>PRODUCT APPLICATION</b>	Primary side transformer protection
<b>RATED FREQUENCY - MAX</b>	50 Hz
<b>RATED FREQUENCY - MIN</b>	50 Hz
<b>RELEASE CHARACTERISTIC</b>	Other
<b>STANDARD</b>	DIN
<b>UTILIZATION CATEGORY</b>	Other
<b>VOLTAGE TYPE</b>	AC
<b>WITH STRIKER</b>	Yes
<b>CLASS</b>	Class back-up
<b>PRE ARC (I2T)</b>	8 x 100
<b>RESISTANCE</b>	31.1 Ohms
<b>WATT LOSSES</b>	76 W
<b>FUSE DIAMETER</b>	51 mm
<b>INTERRUPT RATING</b>	35.5 kAIC
<b>CONSTRUCTION SIZE</b>	51 x 292 mm
<b>MOUNTING METHOD</b>	Clip-in
<b>VOLTAGE RATING</b>	17.5 kV
<b>TYPE</b>	Fuse
<b>APPLICATION</b>	<ul style="list-style-type: none"> <li>• transformer protection</li> <li>• indoor or outdoor use</li> </ul>
<b>FUSE TYPE</b>	TDLSj

