



□□□□□

Eaton 170E2161

Fuse-link, high speed, 100 A, AC 500 V, 45 x 45 x 141 mm, aR, IEC, with indicator

□□□□

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170E2161
UPC	051712209090
PRODUCT LENGTH/DEPTH	290 mm
PRODUCT HEIGHT	62 mm
PRODUCT WIDTH	142 mm
PRODUCT WEIGHT	833 g
COMPLIANCES	Contact factory RoHS Compliant

□□□□	
AMPERAGE RATING	100 A
BREAKING CAPACITY	220 kA
FUSE INDICATOR	Top fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC/DC
FUSE SIZE	Other
RATED VOLTAGE AC	500 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	111 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	M10
CLASS	Class aR
WATT LOSSES	22 W
FUSE SHAPE	Square body, center bolted tags
COLOR	None
INTERRUPT RATING	200 kAIC
CONSTRUCTION SIZE	Other
PACKAGING TYPE	Standard
VOLTAGE RATING	500 V
TYPE	Fuse
APPLICATION	diode protection
FUSE TYPE	Bolted tag
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

□□□□:
□□□□:
□□□:
□□:

□□	
DECLARATIONS OF CONFORMITY	eaton-high-speed-square-body-fuse-declaration-of-conformity-uk251153en.pdf