


## Eaton 170E3586

Eaton Bussmann series high speed traction fuse, 125A, 100 kAIC, Other, Fuse, Class gR

PRODUCT NAME	Eaton Bussmann series high speed traction fuse
CATALOG NUMBER	170E3586
UPC	051712209281
PRODUCT LENGTH/DEPTH	129 mm
PRODUCT HEIGHT	61 mm
PRODUCT WIDTH	43 mm
PRODUCT WEIGHT	942 g
COMPLIANCES	RoHS Compliant IEC

AMPERAGE RATING	125 A
BREAKING CAPACITY	100 kA
VOLTAGE TYPE	DC
UTILIZATION CATEGORY	gR (general purpose semiconductor protection)
INSULATED METAL GRIPPING LUGS (IMGL)	No
FUSE INDICATOR	Other
FUSE SIZE	1*
CLASS	Class gR
WATT LOSSES	21 W
FUSE SHAPE	Square body, slotted center bolted tags
PRE ARC (I2T)	4500
MOUNTING DIMENSION	M8
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	156 mm
CURRENT TYPE	DC
RATED VOLTAGE DC	750 V
COLOR	None
INTERRUPT RATING	100 kAIC
CONSTRUCTION SIZE	Other
PACKAGING TYPE	Standard
VOLTAGE RATING	750 V
TYPE	Fuse
APPLICATION	traction
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com  
© 2025

Follow us on social media to get the latest product and support information.

