

Eaton 170E3956

Fuse-link, high speed, 80 A, DC 2000 V, 40 kA, compact size 1, 55 x 77 x 416 mm, gR, IEC, type K indicator

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170E3956
UPC	051712209571
PRODUCT LENGTH/DEPTH	5.433 in
PRODUCT HEIGHT	2.087 in
PRODUCT WIDTH	0.315 in
PRODUCT WEIGHT	1.6456 lb
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	IEC

AMPERAGE RATING	80 A
FUSE INDICATOR	Non Indicating
FUSE SIZE	1*
CLASS	Class aR
WATT LOSSES	50 W
INTERRUPT RATING	100 kAIC at 1200 Vdc
PACKAGING TYPE	Standard
VOLTAGE RATING	2000 V
TYPE	Fuse
APPLICATION	DC common bus, DC drives, power converters/rectifiers, reduced voltage starters
FUSE TYPE	Bolted tag

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

