



Eaton 170E5399

Fuse-link, high speed, 100 A, AC 1600 V,
special DIN 1, aR, DIN, IEC, with indicator

□□□□

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170E5399
UPC	051712212021
PRODUCT LENGTH/DEPTH	154 mm
PRODUCT HEIGHT	79 mm
PRODUCT WIDTH	196 mm
PRODUCT WEIGHT	192.5 g
COMPLIANCES	EAC
CERTIFICATIONS	IEC

□□□□	
AMPERAGE RATING	100 A
BREAKING CAPACITY	100 kA
FUSE INDICATOR	Top fuse status indicator
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
FUSE SIZE	1
RATED VOLTAGE AC	1600 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	168 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	M10
CLASS	Class aR
WATT LOSSES	38 W
FUSE SHAPE	Square body, slotted center bolted tags
COLOR	None
INTERRUPT RATING	100 kAIC
CONSTRUCTION SIZE	1
PACKAGING TYPE	Standard
VOLTAGE RATING	1600 V
TYPE	Fuse
FUSE TYPE	Bolted tag DIN 43653
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

□□

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
□□:



□□□□
Eaton House
30 Pembroke Road
Dublin 4, □□□
Eaton.com

© 2025 □□ □□□□□□

Follow us on social media to get the latest product and support information.

