



Eaton 170E8078

Fuse-link, high speed, 550 A, AC 1000 V, DIN 2, aR, DIN, with indicator

□□□□

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170E8078
UPC	051712213813
PRODUCT LENGTH/DEPTH	280 mm
PRODUCT HEIGHT	65 mm
PRODUCT WIDTH	180 mm
PRODUCT WEIGHT	1883 g
COMPLIANCES	Contact factory RoHS Compliant

□□□□	
AMPERAGE RATING	550 A
BREAKING CAPACITY	100 kA
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	2
RATED VOLTAGE AC	1000 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	108 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	M10
CLASS	Class aR
WATT LOSSES	108 W
FUSE SHAPE	Square body, slotted center bolted tags
COLOR	None
CONSTRUCTION SIZE	2
PACKAGING TYPE	Standard
VOLTAGE RATING	1000 V
TYPE	Fuse
FUSE TYPE	Bolted tag DIN 43653
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
□□:

□□	
DECLARATIONS OF CONFORMITY	eaton-high-speed-square-body-fuse-declaration-of-conformity-uk251153en.pdf