



## Eaton 170F8234

Eaton Bussmann series high speed traction fuse, 400A, 100 kAIC, Other, Fuse, Class aR

□□□□

<b>PRODUCT NAME</b>	Eaton Bussmann series high speed traction fuse
<b>CATALOG NUMBER</b>	170F8234
<b>UPC</b>	051712272223
<b>PRODUCT LENGTH/DEPTH</b>	165 mm
<b>PRODUCT HEIGHT</b>	90 mm
<b>PRODUCT WIDTH</b>	66 mm
<b>PRODUCT WEIGHT</b>	1051 g
<b>CERTIFICATIONS</b>	IEC

## □□□□

<b>AMPERAGE RATING</b>	400 A
<b>BREAKING CAPACITY</b>	100 kA
<b>VOLTAGE TYPE</b>	DC
<b>UTILIZATION CATEGORY</b>	aR (accompanied semiconductor protection)
<b>INSULATED METAL GRIPPING LUGS (IMGL)</b>	No
<b>FUSE INDICATOR</b>	Other
<b>FUSE SIZE</b>	2
<b>CLASS</b>	Class aR
<b>CLEARING (I2T)</b>	310000 at 1000 Vdc
<b>WATT LOSSES</b>	120 W
<b>FUSE SHAPE</b>	Square body, offset bolted tags
<b>MOUNTING DIMENSION</b>	M8
<b>CENTER-TO-CENTER DISTANCE OF CONNECTIONS</b>	142 mm
<b>CURRENT TYPE</b>	DC
<b>RATED VOLTAGE DC</b>	1200 V
<b>COLOR</b>	None
<b>INTERRUPT RATING</b>	100 kAIC
<b>CONSTRUCTION SIZE</b>	2
<b>PACKAGING TYPE</b>	Standard
<b>VOLTAGE RATING</b>	1200 V
<b>TYPE</b>	Fuse
<b>APPLICATION</b>	traction
<b>FITTED WITH:</b>	Double slot tags
<b>FUSE SYSTEM (ACCORDING TO IEC 60269)</b>	Other

## □□

DECLARATIONS OF CONFORMITY

[eaton-high-speed-square-body-fuse-declaration-of-conformity-uk251153en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



  Eaton House  
30 Pembroke Road  
Dublin 4,    
Eaton.com

© 2025    

Follow us on social media to get the latest product and support information.

