

Eaton 170H3004

Eaton Bussmann series high speed fuse base, 1000 Vac/Vdc, 1250A, fixed centre fuse base (80mm)

PRODUCT NAME	Eaton Bussmann series high speed microswitch
CATALOG NUMBER	170H3004
UPC	051712804653
PRODUCT LENGTH/DEPTH	217 mm
PRODUCT HEIGHT	82 mm
PRODUCT WIDTH	94 mm
PRODUCT WEIGHT	1339 g
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	UL 512

AMPERAGE RATING	1250 A
NUMBER OF POLES	Single-pole
SWIVELLING MECHANISM	No
FEATURES	Halogen free
ACCESSORY/SPARE PART TYPE	Fixed centre fuse base
FITTED WITH:	Extra contact
CONNECTION	Screw connection 80 mm Centre distance
CONSTRUCTION SIZE	Other
MOUNTING METHOD	Screw-on
QUANTITY	1
VOLTAGE RATING	1000 Vac, 1000 Vdc
VOLTAGE RATING - MAX	1000 V
CONNECTION TYPE	Connector M10
TYPE	Fuse accessory
APPLICATION	High speed/semiconductor fuses rated up 690V (IEC)/700V (UL)
SUITABLE FOR	DIN 43653 Square body fuses size 1* to 3

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:

[eaton-fuses-fuse-base-dimensions.eps](#)



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

