

Eaton 170L5701

Fuse-link, high speed, 500 A, AC 660 V, Size 1, 51 x 51 x 138 mm, aR, IEC, single indicator

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170L5701
UPC	051712811811
PRODUCT LENGTH/DEPTH	62 mm
PRODUCT HEIGHT	142 mm
PRODUCT WIDTH	230 mm
PRODUCT WEIGHT	1050 g
COMPLIANCES	Contact factory RoHS Compliant

AMPERAGE RATING	500 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	Top fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	1
RATED VOLTAGE AC	660 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	108 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	M10
CLASS	Class aR
WATT LOSSES	80 W
FUSE SHAPE	Square body, slotted center bolted tags
COLOR	None
INTERRUPT RATING	200 kAIC
CONSTRUCTION SIZE	1
PACKAGING TYPE	Standard
VOLTAGE RATING	660 V
TYPE	Fuse
APPLICATION	semiconductor protection
FUSE TYPE	Bolted tag
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

DECLARATIONS OF CONFORMITY

[eaton-high-speed-square-body-fuse-declaration-of-conformity-uk251153en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

