



## Eaton 170L5819

Fuse-link, high speed, 50 A, AC 660 V, DIN 00, 30 x 60 x 78 mm, aR, DIN, IEC, single indicator

□□□□

<b>PRODUCT NAME</b>	Eaton Bussmann series high speed square body fuse
<b>CATALOG NUMBER</b>	170L5819
<b>UPC</b>	051712215961
<b>PRODUCT LENGTH/DEPTH</b>	217 mm
<b>PRODUCT HEIGHT</b>	65 mm
<b>PRODUCT WIDTH</b>	85 mm
<b>PRODUCT WEIGHT</b>	207.3333333 g
<b>COMPLIANCES</b>	Contact factory RoHS Compliant

□□□□	
AMPERAGE RATING	50 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	Top fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	00
RATED VOLTAGE AC	660 V
CURRENT TYPE	AC
CLASS	Class aR
WATT LOSSES	10 W
FUSE SHAPE	Square body, knife blade contacts
COLOR	None
INTERRUPT RATING	200 kAIC
CONSTRUCTION SIZE	00
PACKAGING TYPE	Standard
VOLTAGE RATING	660 V
TYPE	Fuse
APPLICATION	semiconductor protection
FUSE TYPE	DIN 43620 Bladed
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
□□:

□□	
DECLARATIONS OF CONFORMITY	<a href="#">eaton-high-speed-square-body-fuse-declaration-of-conformity-uk251153en.pdf</a>



□□□□  
Eaton House  
30 Pembroke Road  
Dublin 4, □□□  
Eaton.com

© 2025 □□ □□□□□□

Follow us on social media to get the latest product and support information.

