



Eaton 170L9572

Fuse-link, high speed, 400 A, AC 1000 V, Size 3, 76 x 92 x 75 mm, aR, IEC, single indicator

□□□□

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170L9572
PRODUCT LENGTH/DEPTH	168 mm
PRODUCT HEIGHT	76 mm
PRODUCT WIDTH	95 mm
PRODUCT WEIGHT	705.5 g
COMPLIANCES	CE RoHS Compliant EAC
CERTIFICATIONS	IEC 60269-4

□□□□

AMPERAGE RATING	400 A
BREAKING CAPACITY	125 kA
FUSE INDICATOR	Centre fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	3
RATED VOLTAGE AC	1000 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	75.4 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	M12
CLASS	Class aR
WATT LOSSES	112 W
FUSE SHAPE	Square body, flush end contacts
COLOR	None
INTERRUPT RATING	125 kAIC
CONSTRUCTION SIZE	3
PACKAGING TYPE	Standard
VOLTAGE RATING	1000 V
TYPE	Fuse
APPLICATION	semiconductor protection
FUSE TYPE	Flush end
FUSE SYSTEM (ACCORDING TO IEC 60269)	IEC 60269-4 flush end connections type A

□□

DECLARATIONS OF CONFORMITY

[eaton-high-speed-square-body-fuse-declaration-of-conformity-uk251153en.pdf](#)

