

Eaton 170L9655

Fuse-link, high speed, 800 A, AC 1000 V, Size 3, 74 x 92 x 141 mm, aR, DIN, IEC, single indicator

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170L9655
UPC	051712812252
PRODUCT LENGTH/DEPTH	168 mm
PRODUCT HEIGHT	76 mm
PRODUCT WIDTH	95 mm
PRODUCT WEIGHT	1281 g
COMPLIANCES	Contact factory RoHS Compliant

AMPERAGE RATING	800 A
BREAKING CAPACITY	100 kA
FUSE INDICATOR	Centre fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	3
RATED VOLTAGE AC	1000 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	108 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	M10
CLASS	Class aR
WATT LOSSES	135 W
FUSE SHAPE	Square body, slotted center bolted tags
COLOR	None
CONSTRUCTION SIZE	3
PACKAGING TYPE	Standard
VOLTAGE RATING	1000 V
TYPE	Fuse
APPLICATION	semiconductor protection
FUSE TYPE	Bolted tag DIN 43653
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

DECLARATIONS OF CONFORMITY

[eaton-high-speed-square-body-fuse-declaration-of-conformity-uk251153en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

