

# Eaton 170M0161

Fuse-link, high speed, 25 A, AC 660 V, size 0000, 18 x 19 x 100 mm, gR, UL, visual indicator

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M0161
UPC	051712815635
PRODUCT LENGTH/DEPTH	100 mm
PRODUCT HEIGHT	18 mm
PRODUCT WIDTH	19 mm
PRODUCT WEIGHT	52.5 g
COMPLIANCES	RoHS Compliant CE Marked
CERTIFICATIONS	UL Recognized IEC 60269

<b>AMPERAGE RATING</b>	25 A
<b>BREAKING CAPACITY</b>	200 kA
<b>FUSE INDICATOR</b>	Top fuse status indicator
<b>INSULATED METAL GRIPPING LUGS (IMGL)</b>	No
<b>UTILIZATION CATEGORY</b>	gR (general purpose semiconductor protection)
<b>VOLTAGE TYPE</b>	AC
<b>FUSE SIZE</b>	0000
<b>RATED VOLTAGE AC</b>	660 V
<b>CENTER-TO-CENTER DISTANCE OF CONNECTIONS</b>	78 mm
<b>CURRENT TYPE</b>	AC
<b>MOUNTING DIMENSION</b>	M8
<b>CLASS</b>	Class gR
<b>WATT LOSSES</b>	8 W
<b>FUSE SHAPE</b>	Square body, slotted offset bolted tags
<b>COLOR</b>	None
<b>INTERRUPT RATING</b>	200 kAIC
<b>CONSTRUCTION SIZE</b>	0000
<b>PACKAGING TYPE</b>	Standard
<b>VOLTAGE RATING</b>	660 V
<b>TYPE</b>	Fuse
<b>APPLICATION</b>	semiconductor protection
<b>FUSE TYPE</b>	Bolted tag
<b>FUSE SYSTEM (ACCORDING TO IEC 60269)</b>	Other

<b>DECLARATIONS OF CONFORMITY</b>	<a href="#">eaton-high-speed-square-body-fuse-declaration-of-conformity-uk251153en.pdf</a>
-----------------------------------	--

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

