



Eaton 170M1830

Eaton Bussmann series Fuse-link, high speed, 350 A, AC 1000 V, size 230, 24 x 78 x 115 mm, aR, IEC

□□□□

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M1830
PRODUCT LENGTH/DEPTH	115 mm
PRODUCT HEIGHT	24 mm
PRODUCT WIDTH	74 mm
PRODUCT WEIGHT	283 g
COMPLIANCES	CE RoHS Compliant EAC
CERTIFICATIONS	IEC 60269-4 UL 248-13

□□□□	
AMPERAGE RATING	350 A
BREAKING CAPACITY	50 kA
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	DC
FUSE SIZE	Other
RATED VOLTAGE DC	1000 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	92.3 mm
CURRENT TYPE	DC
MOUNTING DIMENSION	M8
CLASS	Class aR
WATT LOSSES	75 W
COLOR	None
INTERRUPT RATING	50 kAIC
CONSTRUCTION SIZE	Other
PACKAGING TYPE	Standard
VOLTAGE RATING	1000 V
TYPE	Fuse
FUSE TYPE	FU/Without indicator
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

□□□□:
□□□□:
□□□:
□□:

□□	
DECLARATIONS OF CONFORMITY	eaton-high-speed-square-body-fuse-declaration-of-conformity-uk251153en.pdf