



Eaton 170M2677

Fuse-link, high speed, 40 A, AC 1000 V, DIN 00, aR, DIN, IEC, single indicator, live gripping lugs

□□□□

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M2677
UPC	051712671705
PRODUCT LENGTH/DEPTH	79 mm
PRODUCT HEIGHT	60 mm
PRODUCT WIDTH	30 mm
PRODUCT WEIGHT	207.5 g
COMPLIANCES	Contact factory RoHS Compliant



Powering Business Worldwide

□□□□

AMPERAGE RATING	40 A
BREAKING CAPACITY	125 kA
FUSE INDICATOR	Top fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	00
RATED VOLTAGE AC	1000 V
CURRENT TYPE	AC
CLASS	Class aR
WATT LOSSES	13 W
FUSE SHAPE	Square body, knife blade contacts
COLOR	None
INTERRUPT RATING	125 kAIC
FITTED WITH:	Type T Indicator for micro
CONSTRUCTION SIZE	00
PACKAGING TYPE	Standard
VOLTAGE RATING	1000 V (IEC)
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	DIN 43620 T indicator for micro Bladed
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

□□

DECLARATIONS OF
CONFORMITY

[eaton-high-speed-square-body-fuse-declaration-of-conformity-uk251013en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

