



Eaton 170M2684

Fuse-link, high speed, 200 A, AC 900 V, DIN 00, aR, DIN, IEC, single indicator



PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M2684
UPC	051712678537
PRODUCT LENGTH/DEPTH	217 mm
PRODUCT HEIGHT	65 mm
PRODUCT WIDTH	85 mm
PRODUCT WEIGHT	225 g
COMPLIANCES	Contact factory RoHS Compliant



Powering Business Worldwide

□□□□

AMPERAGE RATING	200 A
BREAKING CAPACITY	125 kA
FUSE INDICATOR	Top fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	00
RATED VOLTAGE AC	900 V
CURRENT TYPE	AC
CLASS	Class aR
WATT LOSSES	31 W
FUSE SHAPE	Square body, knife blade contacts
COLOR	None
INTERRUPT RATING	125 kAIC
FITTED WITH:	Type T Indicator for micro
CONSTRUCTION SIZE	00
PACKAGING TYPE	Standard
VOLTAGE RATING	900 V (IEC)
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	DIN 43620 T indicator for micro Bladed
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

□□

