

Eaton 170M2715

Fuse-link, high speed, 125 A, AC 690 V, size 00, 30 x 48 x 64 mm, aR, IEC, visual indicator

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M2715
PRODUCT LENGTH/DEPTH	64 mm
PRODUCT HEIGHT	62 mm
PRODUCT WIDTH	30 mm
PRODUCT WEIGHT	211 g
COMPLIANCES	CE

AMPERAGE RATING	125 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	Top fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	00
RATED VOLTAGE AC	690 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	64 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	M8
CLASS	Class aR
WATT LOSSES	25 W
FUSE SHAPE	Square body, flush end contacts
COLOR	None
INTERRUPT RATING	200 kAIC
CONSTRUCTION SIZE	00
PACKAGING TYPE	Standard
VOLTAGE RATING	690 V
TYPE	Fuse
APPLICATION	semiconductor protection
FUSE TYPE	Flush end
FUSE SYSTEM (ACCORDING TO IEC 60269)	IEC 60269-4 flush end connections type A



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

