



Eaton 170M3318

Fuse-link, high speed, 350 A, AC 690 V, compact size 1, 45 x 59 x 102 mm, aR, IEC, UL, visual indicator

□□□□

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M3318
UPC	051712255677
PRODUCT LENGTH/DEPTH	305 mm
PRODUCT HEIGHT	65 mm
PRODUCT WIDTH	145 mm
PRODUCT WEIGHT	301 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC Rated UL Recognized



Powering Business Worldwide

□□□□	
AMPERAGE RATING	350 A
FUSE INDICATOR	Non Indicating
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	1*
CLASS	Class aR
CLEARING (I2T)	68500 at 660 V
WATT LOSSES	55 W
PRE ARC (I2T)	10000
INTERRUPT RATING	200 kAIC
FITTED WITH:	Type T Indicator for micro
PACKAGING TYPE	Standard
VOLTAGE RATING	700 V (UL), 690 V (IEC)
TYPE	Square body, French style -E/ type T indicator for micro
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	French style E/Type indicator for micro

□□	
DECLARATIONS OF CONFORMITY	eaton-high-speed-square-body-fuse-declaration-of-conformity-uk250915en.pdf

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
□□:



□□□□
 Eaton House
 30 Pembroke Road
 Dublin 4, □□□
 Eaton.com

© 2025 □□ □□□□□□

Follow us on social media to get the latest product and support information.

