



Eaton 170M3360

Fuse-link, high speed, 63 A, AC 690 V,
compact size 1, 45 x 59 x 102 mm, aR, IEC,
UL, single indicator

□□□□

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M3360
UPC	051712255738
PRODUCT LENGTH/DEPTH	168 mm
PRODUCT HEIGHT	80 mm
PRODUCT WIDTH	124 mm
PRODUCT WEIGHT	705 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC Rated UL Recognized

□□□□

AMPERAGE RATING	63 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	Centre fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	1*
RATED VOLTAGE AC	690 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	76 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	M8
CLASS	Class aR
CLEARING (I ₂ T)	770 at 660 V
WATT LOSSES	14 W
FUSE SHAPE	Square body, slotted center bolted tags
PRE ARC (I ₂ T)	115
COLOR	None
INTERRUPT RATING	200 kAIC
FITTED WITH:	Type K Indicator for micro
CONSTRUCTION SIZE	Other
PACKAGING TYPE	Standard
VOLTAGE RATING	690 V
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	French style EKN/Type K Indicator for Micro Bolted tag
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

□□

DECLARATIONS OF CONFORMITY

[eaton-high-speed-square-body-fuse-declaration-of-conformity-uk250915en.pdf](#)

[eaton-high-speed-square-body-fuse-declaration-of-conformity-uk250913en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

