

Eaton 170M3470

Fuse-link, high speed, 450 A, AC 690 V,
compact size 1, aR, IEC, UL, single indicator

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M3470
UPC	051712256216
PRODUCT LENGTH/DEPTH	60 mm
PRODUCT HEIGHT	50 mm
PRODUCT WIDTH	43 mm
PRODUCT WEIGHT	267 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	UL Recognized IEC Rated

AMPERAGE RATING	450 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	Centre fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	1*
RATED VOLTAGE AC	690 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	50 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	M8
CLASS	Class aR
CLEARING (I2T)	140000 at 660 V
WATT LOSSES	65 W
FUSE SHAPE	Square body, flush end contacts
PRE ARC (I2T)	115
COLOR	None
INTERRUPT RATING	200 kAIC
FITTED WITH:	Type K Indicator for micro
CONSTRUCTION SIZE	Other
MOUNTING METHOD	Flush
PACKAGING TYPE	Standard
VOLTAGE RATING	690 V (IEC), 700 V (UL)
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	Flush end BKN/Type K Indicator for Micro
FUSE SYSTEM (ACCORDING TO IEC 60269)	IEC 60269-4 flush end connections type A

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

