

## Eaton 170M3515

Eaton Bussmann series high speed square body fuse, 200A 690V 1\*GN/50 AR UC

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M3515
UPC	051712256407
PRODUCT LENGTH/DEPTH	45 mm
PRODUCT HEIGHT	90 mm
PRODUCT WIDTH	155 mm
PRODUCT WEIGHT	525 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	UL Recognized IEC Rated

<b>AMPERAGE RATING</b>	200 A
<b>FUSE INDICATOR</b>	Non Indicating
<b>UTILIZATION CATEGORY</b>	aR (accompanied semiconductor protection)
<b>VOLTAGE TYPE</b>	AC
<b>FUSE SIZE</b>	1*
<b>CLASS</b>	Class aR
<b>CLEARING (I2T)</b>	15000 at 660 V
<b>WATT LOSSES</b>	47 W
<b>FUSE SHAPE</b>	Square Body size 1* to 3, flush-end contact
<b>PRE ARC (I2T)</b>	2200
<b>INTERRUPT RATING</b>	200 kAIC
<b>CONNECTION</b>	Flush-end contact
<b>MOUNTING METHOD</b>	Flush
<b>PACKAGING TYPE</b>	Standard
<b>VOLTAGE RATING</b>	1300 V (UL), 1250 V (IEC)
<b>TYPE</b>	Square body -G/- visual indicator
<b>APPLICATION</b>	DC common bus DC drives power converters/rectifiers
<b>FUSE TYPE</b>	Flush end G/Visual indicator

## DECLARATIONS OF CONFORMITY

[eaton-high-speed-square-body-fuse-declaration-of-conformity-uk250913en.pdf](#)

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

