



Eaton 170M3523

Eaton Bussmann series square body fuse,
Visual indicator 200 kA Flush-end contact US
thread Square body Power
converters/rectifiers and reduced voltage
starters 690V 700V 80W 1 630A

□□□□

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M3523
UPC	051712256483
PRODUCT LENGTH/DEPTH	58.93 mm
PRODUCT HEIGHT	50.8 mm
PRODUCT WIDTH	44.96 mm
PRODUCT WEIGHT	255 g
COMPLIANCES	CE Marked
CERTIFICATIONS	UL Recognized IEC Rated CSA Certified



Powering Business Worldwide

USED WITH	Power converters/rectifiers and reduced voltage starters
AMPERAGE RATING	630 A
FUSE INDICATOR	Non Indicating
FUSE SIZE	1
CLASS	Class aR
CLEARING (I2T)	48500 at 325000 V
WATT LOSSES	80 W
PRE ARC (I2T)	48500
INTERRUPT RATING	200 kAIC
MOUNTING METHOD	Flush-end contact Imperial thread
PACKAGING TYPE	Standard
VOLTAGE RATING	690 V, 700 V
TYPE	Square body -G/- visual indicator
APPLICATION	DC common bus DC drives power converters/rectifiers

□□□□:

□□□□:

□□□:

□□: