



00000

Eaton 170M3533

Fuse-link, high speed, 80 A, AC 1000 V,
compact size 1, aR, IEC, single indicator

00000

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M3533
UPC	051712678575
PRODUCT LENGTH/DEPTH	111 mm
PRODUCT HEIGHT	60 mm
PRODUCT WIDTH	43 mm
PRODUCT WEIGHT	464 g
COMPLIANCES	RoHS Compliant EAC CE
CERTIFICATIONS	IEC 60269-4

□□□

AMPERAGE RATING	80 A
BREAKING CAPACITY	125 kA
FUSE INDICATOR	Centre fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	1*
RATED VOLTAGE AC	1000 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	116 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	M10
CLASS	Class aR
CLEARING (I₂T)	2750 at 1000 V
WATT LOSSES	30 W
FUSE SHAPE	Square body, center bolted tags
PRE ARC (I₂T)	460
COLOR	None
INTERRUPT RATING	125 kAIC
FITTED WITH:	Type K Indicator for micro
CONSTRUCTION SIZE	Other
PACKAGING TYPE	Standard
VOLTAGE RATING	1000 V
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	US Style FKE/115 Type K indicator for micro
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

□□

DECLARATIONS OF CONFORMITY

eaton-high-speed-square-body-fuse-declaration-of-conformity-uk250916en.pdf

□□□□:

□□□□⋮

10

11

EATON
Powering Business Worldwide

□□□□ Eaton House
30 Pembroke Road
Dublin 4, □□□
Eaton.com

© 2026

