


## Eaton 170M3903

Eaton Bussmann series high speed square body fuse, 160 A, 690 V, 108 Millimeter, Size 1\*, Top fuse status indicator

|                      |                                                   |
|----------------------|---------------------------------------------------|
|                      |                                                   |
| PRODUCT NAME         | Eaton Bussmann series high speed square body fuse |
| CATALOG NUMBER       | 170M3903                                          |
| UPC                  | 051712563178                                      |
| PRODUCT LENGTH/DEPTH | 145 mm                                            |
| PRODUCT HEIGHT       | 65 mm                                             |
| PRODUCT WIDTH        | 305 mm                                            |
| PRODUCT WEIGHT       | 347 g                                             |
| COMPLIANCES          | Contact factory<br>RoHS Compliant                 |

|                                          |                                           |
|------------------------------------------|-------------------------------------------|
|                                          |                                           |
| AMPERAGE RATING                          | 160 A                                     |
| BREAKING CAPACITY                        | 200 kA                                    |
| FUSE INDICATOR                           | Top fuse status indicator                 |
| INSULATED METAL GRIPPING LUGS (IMGL)     | No                                        |
| UTILIZATION CATEGORY                     | aR (accompanied semiconductor protection) |
| VOLTAGE TYPE                             | AC                                        |
| FUSE SIZE                                | 1*                                        |
| RATED VOLTAGE AC                         | 690 V                                     |
| CENTER-TO-CENTER DISTANCE OF CONNECTIONS | 108 mm                                    |
| CURRENT TYPE                             | AC                                        |
| MOUNTING DIMENSION                       | M10                                       |
| CLASS                                    | Class aR                                  |
| WATT LOSSES                              | 30 W                                      |
| FUSE SHAPE                               | Square body, slotted center bolted tags   |
| COLOR                                    | None                                      |
| INTERRUPT RATING                         | 200 kAIC                                  |
| CONSTRUCTION SIZE                        | Other                                     |
| PACKAGING TYPE                           | Standard                                  |
| VOLTAGE RATING                           | 690 V                                     |
| TYPE                                     | Fuse                                      |
| APPLICATION                              | semiconductor protection                  |
| FUSE TYPE                                | Bolted tag                                |
| FUSE SYSTEM (ACCORDING TO IEC 60269)     | Other                                     |



|                 |
|-----------------|
| PROJECT NAME:   |
| PROJECT NUMBER: |
| PREPARED BY:    |
| :               |



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

