



Eaton 170M3930

Eaton Bussmann series square body fuse, Adapter type indicator mounted on fuse for microswitch North position 150 kA Flush-end contact US thread Square body Power converters/rectifiers and reduced voltage starters 1000V 65W 1 350A

□□□□

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M3930
UPC	051712678742
PRODUCT LENGTH/DEPTH	61 mm
PRODUCT HEIGHT	74 mm
PRODUCT WIDTH	43 mm
PRODUCT WEIGHT	392.25 g
COMPLIANCES	CE Marked
CERTIFICATIONS	IEC Rated CSA Certified UL Recognized



Powering Business Worldwide

USED WITH	Power converters/rectifiers and reduced voltage starters
AMPERAGE RATING	350 A
FUSE INDICATOR	Non Indicating
FUSE SIZE	1
CLASS	Class aR
CLEARING (I2T)	29000 at 175000 V
WATT LOSSES	65 W
PRE ARC (I2T)	29000
INTERRUPT RATING	150 kAIC
MOUNTING METHOD	Flush-end contact Imperial thread
PACKAGING TYPE	Standard
VOLTAGE RATING	1000 V
TYPE	Square body flush end contact -BKN/- type T indicator for micro
APPLICATION	DC common bus DC drives power converters/rectifiers reduced voltage starters

□□□□:

□□□□:

□□□:

□□: