



## Eaton 170M4008

Fuse-link, high speed, 200 A, AC 690 V, DIN 1, 53 x 53 x 108 mm, aR, DIN, IEC, single indicator

□□□□

|                                 |                                                         |
|---------------------------------|---------------------------------------------------------|
| <b>PRODUCT NAME</b>             | Eaton Bussmann series<br>high speed square body<br>fuse |
| <b>CATALOG NUMBER</b>           | 170M4008                                                |
| <b>UPC</b>                      | 051712257404                                            |
| <b>PRODUCT<br/>LENGTH/DEPTH</b> | 245 mm                                                  |
| <b>PRODUCT HEIGHT</b>           | 62 mm                                                   |
| <b>PRODUCT WIDTH</b>            | 142 mm                                                  |
| <b>PRODUCT WEIGHT</b>           | 455 g                                                   |
| <b>COMPLIANCES</b>              | CE Marked<br>RoHS Compliant                             |
| <b>CERTIFICATIONS</b>           | UL Recognized<br>IEC Rated                              |

## □□□□

|                                          |                                                                      |
|------------------------------------------|----------------------------------------------------------------------|
| AMPERAGE RATING                          | 200 A                                                                |
| BREAKING CAPACITY                        | 200 kA                                                               |
| FUSE INDICATOR                           | Top fuse status indicator                                            |
| INSULATED METAL GRIPPING LUGS (IMGL)     | No                                                                   |
| UTILIZATION CATEGORY                     | aR (accompanied semiconductor protection)                            |
| VOLTAGE TYPE                             | AC                                                                   |
| FUSE SIZE                                | 1                                                                    |
| RATED VOLTAGE AC                         | 690 V                                                                |
| CENTER-TO-CENTER DISTANCE OF CONNECTIONS | 78 mm                                                                |
| CURRENT TYPE                             | AC                                                                   |
| MOUNTING DIMENSION                       | M10                                                                  |
| CLASS                                    | Class aR                                                             |
| CLEARING (I <sub>2</sub> T)              | 11500 at 660 V                                                       |
| WATT LOSSES                              | 45 W                                                                 |
| CLEARING LOSS                            | 45                                                                   |
| FUSE SHAPE                               | Square body, slotted center bolted tags                              |
| PRE ARC (I <sub>2</sub> T)               | 1650                                                                 |
| COLOR                                    | None                                                                 |
| INTERRUPT RATING                         | 200 kAIC                                                             |
| CONNECTION                               | Blade end x blade end                                                |
| CONSTRUCTION SIZE                        | 1                                                                    |
| PACKAGING TYPE                           | Standard                                                             |
| VOLTAGE RATING                           | 690 V (IEC), 700 V (UL)                                              |
| TYPE                                     | Fuse                                                                 |
| APPLICATION                              | Semiconductor, DC Common bus, DC drives, power converters/rectifiers |
| FUSE TYPE                                | DIN 43653 /80 Visual indicator                                       |
| FUSE SYSTEM (ACCORDING TO IEC 60269)     | Other                                                                |

## □□

|                            |                                                                                            |
|----------------------------|--------------------------------------------------------------------------------------------|
| DECLARATIONS OF CONFORMITY | <a href="#">eaton-high-speed-square-body-fuse-declaration-of-conformity-uk250910en.pdf</a> |
| □□                         | <a href="#">eaton-fuses-fuse-link-dimensions-002.eps</a>                                   |

|                 |
|-----------------|
| PROJECT NAME:   |
| PROJECT NUMBER: |
| PREPARED BY:    |
|                 |



  Eaton House  
30 Pembroke Road  
Dublin 4,    
Eaton.com

© 2025    

Follow us on social media to get the latest product and support information.

