

# Eaton 170M4161

Fuse-link, high speed, 350 A, AC 690 V, DIN 1, 53 x 66 x 138 mm, aR, DIN, IEC, single indicator

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M4161
UPC	051712257879
PRODUCT LENGTH/DEPTH	245 mm
PRODUCT HEIGHT	62 mm
PRODUCT WIDTH	142 mm
PRODUCT WEIGHT	484 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC Rated UL Recognized

<b>AMPERAGE RATING</b>	350 A
<b>BREAKING CAPACITY</b>	200 kA
<b>FUSE INDICATOR</b>	Top fuse status indicator
<b>INSULATED METAL GRIPPING LUGS (IMGL)</b>	No
<b>UTILIZATION CATEGORY</b>	aR (accompanied semiconductor protection)
<b>VOLTAGE TYPE</b>	AC
<b>FUSE SIZE</b>	1
<b>RATED VOLTAGE AC</b>	690 V
<b>CENTER-TO-CENTER DISTANCE OF CONNECTIONS</b>	108 mm
<b>CURRENT TYPE</b>	AC
<b>MOUNTING DIMENSION</b>	M10
<b>CLASS</b>	Class aR
<b>CLEARING (I2T)</b>	59000 at 660 V
<b>WATT LOSSES</b>	60 W
<b>CLEARING LOSS</b>	60
<b>FUSE SHAPE</b>	Square body, slotted center bolted tags
<b>PRE ARC (I2T)</b>	8500
<b>COLOR</b>	None
<b>INTERRUPT RATING</b>	200 kAIC
<b>CONNECTION</b>	Blade end x blade end
<b>CONSTRUCTION SIZE</b>	1
<b>PACKAGING TYPE</b>	Standard
<b>VOLTAGE RATING</b>	690 V (IEC), 700 V (UL)
<b>TYPE</b>	Fuse
<b>APPLICATION</b>	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
<b>FUSE TYPE</b>	DIN 43653 /110 Visual indicator Bolted tag
<b>FUSE SYSTEM (ACCORDING TO IEC 60269)</b>	Other

## DECLARATIONS OF CONFORMITY

[eaton-high-speed-square-body-fuse-declaration-of-conformity-uk250910en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

