

Eaton 170M4180

Eaton Bussmann series high speed square body fuse, 700V (UL), 690V (IEC), 125A, 200 kAIC, Top fuse status indicator, Fuse, Blade end X Din 43-620 blade end, Class gR, DIN 43 620

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M4180
UPC	051712268158
PRODUCT LENGTH/DEPTH	245 mm
PRODUCT HEIGHT	62 mm
PRODUCT WIDTH	142 mm
PRODUCT WEIGHT	399 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	UL Recognized IEC Rated

AMPERAGE RATING	125 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	Top fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	gR (general purpose semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	1
RATED VOLTAGE AC	690 V
CURRENT TYPE	AC
CLASS	Class gR
CLEARING (I2T)	9500 at 600 V
WATT LOSSES	23 W
FUSE SHAPE	Square body, knife blade contacts
PRE ARC (I2T)	1850
COLOR	None
INTERRUPT RATING	200 kAIC
FITTED WITH:	Type T Indicator for micro
CONNECTION	Blade end x Din 43-620 blade end
CONSTRUCTION SIZE	1
PACKAGING TYPE	Standard
VOLTAGE RATING	690 V (IEC)
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	DIN 43620 T indicator for micro Bladed
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

