



## Eaton 170M4317

Eaton Bussmann series square body fuse, Tag-type Indicator for microswitch 200 kA French style blades Square body Power converters/rectifiers and reduced voltage starters 690V 700V 85W 1 700A

### □□□□

|                             |                                                   |
|-----------------------------|---------------------------------------------------|
| <b>PRODUCT NAME</b>         | Eaton Bussmann series high speed square body fuse |
| <b>CATALOG NUMBER</b>       | 170M4317                                          |
| <b>UPC</b>                  | 051712258456                                      |
| <b>PRODUCT LENGTH/DEPTH</b> | 59 mm                                             |
| <b>PRODUCT HEIGHT</b>       | 111 mm                                            |
| <b>PRODUCT WIDTH</b>        | 45 mm                                             |
| <b>PRODUCT WEIGHT</b>       | 295 g                                             |
| <b>COMPLIANCES</b>          | CE Marked                                         |
| <b>CERTIFICATIONS</b>       | CSA Certified<br>UL Recognized<br>IEC Rated       |

|                  |                                                                              |
|------------------|------------------------------------------------------------------------------|
| USED WITH        | Power converters/rectifiers and reduced voltage starters                     |
| AMPERAGE RATING  | 700 A                                                                        |
| FUSE INDICATOR   | Non Indicating                                                               |
| FUSE SIZE        | 1                                                                            |
| CLASS            | Class aR                                                                     |
| CLEARING (I2T)   | 69500 at 465000 V                                                            |
| WATT LOSSES      | 85 W                                                                         |
| PRE ARC (I2T)    | 69500                                                                        |
| INTERRUPT RATING | 200 kAIC                                                                     |
| PACKAGING TYPE   | Standard                                                                     |
| VOLTAGE RATING   | 690 V, 700 V                                                                 |
| TYPE             | Square body French style - E/- type T indicator for microswitch              |
| APPLICATION      | DC common bus DC drives power converters/rectifiers reduced voltage starters |
| FUSE TYPE        | French style                                                                 |

□□□□:

□□□□:

□□□:

□□: