

## Eaton 170M4536

Eaton Bussmann series high speed square body fuse, 400 A, AC 1000 V, size 1, 51 x 68 x 102 mm, aR, IEC, single indicator

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M4536
UPC	051712679138
PRODUCT LENGTH/DEPTH	68 mm
PRODUCT HEIGHT	160 mm
PRODUCT WIDTH	51 mm
PRODUCT WEIGHT	956 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC Rated UL Recognized

AMPERAGE RATING	400 A
BREAKING CAPACITY	100 kA
FUSE INDICATOR	Non Indicating
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
FUSE SIZE	1
RATED VOLTAGE AC	1000 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	102 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	M10
CLASS	Class aR
CLEARING (I2T)	185000 at 1000 V
WATT LOSSES	75 W
FUSE SHAPE	Square Body size 1* to 3, US style
PRE ARC (I2T)	31000
COLOR	None
INTERRUPT RATING	125 kAIC
CONNECTION	Blade end x blade end
CONSTRUCTION SIZE	1
PACKAGING TYPE	Standard
VOLTAGE RATING	1000 V
TYPE	Square body US style - FKE/115 type K indicator for micro
APPLICATION	DC common bus DC drives power converters/rectifiers
FUSE TYPE	FKE/115 Type K indicator for micro
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:

Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

Follow us on social media to get the latest product and support information.