



□□□□□

## Eaton 170M4559

Fuse-link, high speed, 250 A, AC 690 V, size 1,  
53 x 69 x 51 mm, aR, IEC, single indicator

□□□□

<b>PRODUCT NAME</b>	Eaton Bussmann series high speed square body fuse
<b>CATALOG NUMBER</b>	170M4559
<b>UPC</b>	051712259231
<b>PRODUCT LENGTH/DEPTH</b>	73 mm
<b>PRODUCT HEIGHT</b>	52 mm
<b>PRODUCT WIDTH</b>	170 mm
<b>PRODUCT WEIGHT</b>	153 g
<b>COMPLIANCES</b>	CE Marked RoHS Compliant
<b>CERTIFICATIONS</b>	IEC Rated UL Recognized

□□□□

AMPERAGE RATING	250 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	Centre fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	1
RATED VOLTAGE AC	690 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	51 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	Other
CLASS	Class aR
CLEARING (I <sub>2</sub> T)	21000 at 660 V
WATT LOSSES	55 W
FUSE SHAPE	Square body, flush end contacts
PRE ARC (I <sub>2</sub> T)	3100
COLOR	None
INTERRUPT RATING	200 kAIC
CONSTRUCTION SIZE	1
MOUNTING METHOD	Flush
PACKAGING TYPE	Standard
VOLTAGE RATING	690 V
TYPE	Fuse
APPLICATION	semiconductor protection
FUSE TYPE	Flush end
FUSE SYSTEM (ACCORDING TO IEC 60269)	IEC 60269-4 flush end connections type A

□□

DECLARATIONS OF CONFORMITY

[eaton-high-speed-square-body-fuse-declaration-of-conformity-uk250911en.pdf](#)

---

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



  Eaton House  
30 Pembroke Road  
Dublin 4,    
Eaton.com

© 2025    

Follow us on social media to get the latest product and support information.

