



□□□□□

Eaton 170M4569

Fuse-link, high speed, 900 A, AC 550 V, size 1, 53 x 69 x 51 mm, aR, IEC, UL, single indicator, US thread

□□□□

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M4569
UPC	051712259293
PRODUCT LENGTH/DEPTH	73 mm
PRODUCT HEIGHT	52 mm
PRODUCT WIDTH	170 mm
PRODUCT WEIGHT	399.3333333 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC Rated UL Recognized



Powering Business Worldwide

□□□□

AMPERAGE RATING	900 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	Centre fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	1
RATED VOLTAGE AC	550 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	51 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	Other
CLASS	Class aR
CLEARING (I ₂ T)	850000 at 660 V
WATT LOSSES	100 W
FUSE SHAPE	Square body, flush end contacts
PRE ARC (I ₂ T)	155000
COLOR	None
INTERRUPT RATING	200 kAIC
FITTED WITH:	Type K Indicator for micro
CONSTRUCTION SIZE	1
MOUNTING METHOD	Flush
PACKAGING TYPE	Standard
VOLTAGE RATING	550 V
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	Flush end GKN/Type K indicator for micro
FUSE SYSTEM (ACCORDING TO IEC 60269)	IEC 60269-4 flush end connections type A

□□

DECLARATIONS OF CONFORMITY

[eaton-high-speed-square-body-fuse-declaration-of-conformity-uk251153en.pdf](#)

