

Eaton 170M4700

Fuse-link, high speed, 200 A, AC 1250 V, size 1, 53 x 63 x 135 mm, aR, IEC, single indicator

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M4700
UPC	051712793155
PRODUCT LENGTH/DEPTH	245 mm
PRODUCT HEIGHT	62 mm
PRODUCT WIDTH	142 mm
PRODUCT WEIGHT	635 g
COMPLIANCES	Contact factory RoHS Compliant

AMPERAGE RATING	200 A
BREAKING CAPACITY	100 kA
FUSE INDICATOR	Top fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	1
RATED VOLTAGE AC	1250 V
CURRENT TYPE	AC
CLASS	Class aR
WATT LOSSES	50 W
FUSE SHAPE	Square body, special bladed contacts
COLOR	None
INTERRUPT RATING	100 kAIC
CONSTRUCTION SIZE	1
PACKAGING TYPE	Standard
VOLTAGE RATING	1250 V
TYPE	Fuse
APPLICATION	semiconductor protection
FUSE TYPE	T indicator for micro
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:

DECLARATIONS OF CONFORMITY

[eaton-high-speed-square-body-fuse-declaration-of-conformity-uk251153en.pdf](#)



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

