

Eaton 170M5309

Eaton Bussmann series high speed square body fuse, 450 A, 690 V, 90.9 Millimeter, Size 2, Top fuse status indicator

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M5309
UPC	051712260862
PRODUCT LENGTH/DEPTH	210 mm
PRODUCT HEIGHT	80 mm
PRODUCT WIDTH	160 mm
PRODUCT WEIGHT	657 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	UL Recognized IEC Rated

AMPERAGE RATING	450 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	Top fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	2
RATED VOLTAGE AC	690 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	90.9 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	Other
CLASS	Class aR
CLEARING (I2T)	105000 at 660 V
WATT LOSSES	70 W
FUSE SHAPE	Square body, slotted center bolted tags
PRE ARC (I2T)	15500
COLOR	None
INTERRUPT RATING	200 kAIC
FITTED WITH:	Type T Indicator for micro
CONSTRUCTION SIZE	2
PACKAGING TYPE	Standard
VOLTAGE RATING	690 V
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	French style E/Type indicator for micro
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

