

Eaton 170M5314

Fuse-link, high speed, 800 A, AC 690 V, 200 kA, size 2, 61 x 61 x 126 mm, aR, IEC, single indicator, french style

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M5314
UPC	051712260916
PRODUCT LENGTH/DEPTH	12 mm
PRODUCT HEIGHT	126 mm
PRODUCT WIDTH	61 mm
PRODUCT WEIGHT	247.3333333 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	UL Recognized IEC Rated

AMPERAGE RATING	800 A
FUSE INDICATOR	Non Indicating
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	2
CLASS	Class aR
CLEARING (I2T)	575000 at 660 V
WATT LOSSES	105 W
FUSE SHAPE	Square Body size 1* to 3, French style
PRE ARC (I2T)	86000
INTERRUPT RATING	200 kAIC
FITTED WITH:	Type T Indicator for micro
PACKAGING TYPE	Standard
VOLTAGE RATING	700 V (UL), 690 V (IEC)
TYPE	Square body French style - E/ type T indicator for micro
APPLICATION	DC common bus DC drives power converters/rectifiers reduced voltage starters
FUSE TYPE	French style E/Type indicator for micro

DECLARATIONS OF CONFORMITY

[eaton-high-speed-square-body-fuse-declaration-of-conformity-uk251153en.pdf](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

