



Eaton 170M5361

Fuse-link, high speed, 550 A, AC 690 V, size 2, 61 x 77 x 126 mm, aR, IEC, UL, single indicator

□□□□

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M5361
UPC	051712260978
PRODUCT LENGTH/DEPTH	126 mm
PRODUCT HEIGHT	59 mm
PRODUCT WIDTH	84 mm
PRODUCT WEIGHT	610 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	UL Recognized IEC Rated



Powering Business Worldwide



AMPERAGE RATING	550 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	Centre fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	2
RATED VOLTAGE AC	690 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	91 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	Other
CLASS	Class aR
CLEARING (I2T)	300000 at 660 V
WATT LOSSES	80 W
FUSE SHAPE	Square body, slotted center bolted tags
PRE ARC (I2T)	28000
COLOR	None
INTERRUPT RATING	200 kAIC
FITTED WITH:	Type K Indicator for micro
CONSTRUCTION SIZE	2
PACKAGING TYPE	Standard
VOLTAGE RATING	690 V
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	French style EKN/Type K Indicator for Micro Bolted tag
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other



DECLARATIONS OF CONFORMITY

[eaton-high-speed-square-body-fuse-declaration-of-conformity-uk251153en.pdf](#)

