

Eaton 170M5515

Eaton Bussmann series high speed square body fuse, 900 A, 690 V (IEC), 700 V (UL), 50.4 Millimeter, Size 2, Top fuse status indicator

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M5515
UPC	051712261555
PRODUCT LENGTH/DEPTH	168 mm
PRODUCT HEIGHT	80 mm
PRODUCT WIDTH	124 mm
PRODUCT WEIGHT	89.8 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	UL Recognized IEC Rated

AMPERAGE RATING	900 A
BREAKING CAPACITY	200 kA
FUSE INDICATOR	Top fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	2
RATED VOLTAGE AC	690 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	50.4 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	M8
CLASS	Class aR
CLEARING (I2T)	840000 at 660 V
WATT LOSSES	110 W
FUSE SHAPE	Square body, flush end contacts
PRE ARC (I2T)	125000
COLOR	None
INTERRUPT RATING	200 kAIC
CONSTRUCTION SIZE	2
MOUNTING METHOD	Flush
PACKAGING TYPE	Standard
VOLTAGE RATING	690 V (IEC), 700 V (UL)
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	Flush end G/Visual indicator
FUSE SYSTEM (ACCORDING TO IEC 60269)	IEC 60269-4 flush end connections type A



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

