

Eaton 170M5540

Fuse-link, high speed, 800 A, AC 1000 V, size 2, 65 x 180 x 280 mm, aR, IEC, single indicator

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M5540
UPC	051712677837
PRODUCT LENGTH/DEPTH	161 mm
PRODUCT HEIGHT	59 mm
PRODUCT WIDTH	76 mm
PRODUCT WEIGHT	0.45 g
COMPLIANCES	RoHS Compliant
CERTIFICATIONS	IEC Rated

AMPERAGE RATING	800 A
UTILIZATION CATEGORY	gR (general purpose semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	2
CLASS	Class gR
CLEARING (I2T)	1200000 at 1000 V
WATT LOSSES	125 W
PRE ARC (I2T)	195000
INTERRUPT RATING	125 kAIC
FITTED WITH:	Type K Indicator for micro
PACKAGING TYPE	Standard
QUANTITY	2
VOLTAGE RATING	1000 V
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	US Style FKE/115 Type K indicator for micro

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

