



Eaton 170M5567

Eaton Bussmann series high speed square body fuse, 1100 A, AC 600 V, size 2, aR, IEC, UL, single indicator, US thread

□□□□

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M5567
UPC	051712261685
PRODUCT LENGTH/DEPTH	168 mm
PRODUCT HEIGHT	80 mm
PRODUCT WIDTH	124 mm
PRODUCT WEIGHT	828.75 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC Rated UL Recognized

□□□□	
AMPERAGE RATING	1100 A
BREAKING CAPACITY	100 kA
FUSE INDICATOR	Non Indicating
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
FUSE SIZE	2
RATED VOLTAGE AC	600 V
CURRENT TYPE	AC
MOUNTING DIMENSION	M10
CLASS	Class aR
CLEARING (I2T)	1600000 at 600 V
WATT LOSSES	120 W
FUSE SHAPE	Square Body size 1* to 3, flush-end contact
PRE ARC (I2T)	245000
COLOR	None
INTERRUPT RATING	200 kAIC
CONNECTION	Flush-end contact
CONSTRUCTION SIZE	2
MOUNTING METHOD	Flush
PACKAGING TYPE	Standard
VOLTAGE RATING	700 V (UL), 690 V (IEC)
TYPE	Square body -GKN/- type K indicator for micro
APPLICATION	DC common bus DC drives power converters/rectifiers
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

□□□□:
□□□□:
□□□:
□□:

□□	
DECLARATIONS OF CONFORMITY	eaton-high-speed-square-body-fuse-declaration-of-conformity-uk251012en.pdf