

## Eaton 170M5804

Eaton Bussmann series high speed square body fuse, 690 V, 200 A, Fuse size: 2, Top fuse status indicator, DIN 43620, Bladed

<b>PRODUCT NAME</b>	Eaton Bussmann series high speed square body fuse
<b>CATALOG NUMBER</b>	170M5804
<b>UPC</b>	051712579407
<b>PRODUCT LENGTH/DEPTH</b>	210 mm
<b>PRODUCT HEIGHT</b>	80 mm
<b>PRODUCT WIDTH</b>	160 mm
<b>PRODUCT WEIGHT</b>	661 g
<b>COMPLIANCES</b>	Contact factory RoHS Compliant

<b>AMPERAGE RATING</b>	200 A
<b>BREAKING CAPACITY</b>	100 kA
<b>FUSE INDICATOR</b>	Top fuse status indicator
<b>INSULATED METAL GRIPPING LUGS (IMGL)</b>	No
<b>UTILIZATION CATEGORY</b>	aR (accompanied semiconductor protection)
<b>VOLTAGE TYPE</b>	AC
<b>FUSE SIZE</b>	2
<b>RATED VOLTAGE AC</b>	690 V
<b>CURRENT TYPE</b>	AC
<b>CLASS</b>	Class aR
<b>WATT LOSSES</b>	49 W
<b>FUSE SHAPE</b>	Square body, knife blade contacts
<b>COLOR</b>	None
<b>INTERRUPT RATING</b>	100 kAIC
<b>CONSTRUCTION SIZE</b>	Other
<b>PACKAGING TYPE</b>	Standard
<b>VOLTAGE RATING</b>	690 V
<b>TYPE</b>	Fuse
<b>APPLICATION</b>	semiconductor protection
<b>FUSE TYPE</b>	DIN 43620 Bladed
<b>FUSE SYSTEM (ACCORDING TO IEC 60269)</b>	Other

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

:

## DECLARATIONS OF CONFORMITY

[eaton-high-speed-square-body-fuse-declaration-of-conformity-uk251153en.pdf](#)



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

