

Eaton 170M6151

Fuse-link, high speed, 1400 A, AC 1100 V, size 3, 76 x 90 x 139 mm, aR, DIN, IEC, single indicator

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M6151
UPC	051712263030
PRODUCT LENGTH/DEPTH	168 mm
PRODUCT HEIGHT	76 mm
PRODUCT WIDTH	95 mm
PRODUCT WEIGHT	1338 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC Rated UL Recognized



AMPERAGE RATING	1400 A
BREAKING CAPACITY	100 kA
FUSE INDICATOR	Top fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC/DC
FUSE SIZE	3
RATED VOLTAGE AC	1100 V
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	108 mm
CURRENT TYPE	AC
MOUNTING DIMENSION	M10
CLASS	Class aR
CLEARING (I2T)	6000000 at 1000 V
WATT LOSSES	150 W
FUSE SHAPE	Square body, slotted center bolted tags
PRE ARC (I2T)	1250000
COLOR	None
INTERRUPT RATING	100 kAIC
CONSTRUCTION SIZE	3
PACKAGING TYPE	Standard
VOLTAGE RATING	1100 V
TYPE	Fuse
APPLICATION	Semiconductor, DC Common bus, DC drives, power converters/rectifiers
FUSE TYPE	DIN 43653 /110 Visual indicator Bolted tag
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

