



□□□□□

Eaton 170M6202

Fuse-link, high speed, 500 A, AC 1250 V, size 3, 76 x 76 x 150 mm, aR, IEC, single indicator

□□□□

PRODUCT NAME	Eaton Bussmann series high speed square body fuse
CATALOG NUMBER	170M6202
UPC	051712563529
PRODUCT LENGTH/DEPTH	168 mm
PRODUCT HEIGHT	76 mm
PRODUCT WIDTH	95 mm
PRODUCT WEIGHT	1338 g
COMPLIANCES	Contact factory RoHS Compliant

□□□□	
AMPERAGE RATING	500 A
BREAKING CAPACITY	100 kA
FUSE INDICATOR	Top fuse status indicator
INSULATED METAL GRIPPING LUGS (IMGL)	No
UTILIZATION CATEGORY	aR (accompanied semiconductor protection)
VOLTAGE TYPE	AC
FUSE SIZE	3
RATED VOLTAGE AC	1250 V
CURRENT TYPE	AC
CLASS	Class aR
WATT LOSSES	105 W
FUSE SHAPE	Square body, special bladed contacts
COLOR	None
INTERRUPT RATING	100 kAIC
CONSTRUCTION SIZE	3
PACKAGING TYPE	Standard
VOLTAGE RATING	1250 V
TYPE	Fuse
APPLICATION	semiconductor protection
FUSE TYPE	T indicator for micro
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

□□:

□□	
DECLARATIONS OF CONFORMITY	eaton-high-speed-square-body-fuse-declaration-of-conformity-uk251153en.pdf



□□□□
 Eaton House
 30 Pembroke Road
 Dublin 4, □□□
 Eaton.com

© 2025 □□ □□□□□□

Follow us on social media to get the latest product and support information.

